




+ CONNECTORS

USB



✓ Active

TE CONNECTIVITY (TE)

USB, RCPT ASS'Y, V/T, A TYPE,

Universal Serial Bus | A

1734366-4

TE Internal Number: 1734366-4

EU RoHS Compliant

EU ELV Compliant

USB Type A

USB Version 2.0

Size Standard

Connector Style Receptacle

Number of Ports 1

[↓ PRODUCT DRAWING](#)
English

[↓ 3D PDF](#)

DOCUMENTATION

Product Drawings

RECEPT ASSY, VERTICAL, 4 POSITION, THRU-HOLE, TYPE A, USB

PDF

English

CAD Files

3D PDF

PDF

3D

Customer View Model

2D_DXF.ZIP

English

Customer View Model

3D_IGS.ZIP

English

Customer View Model

3D_STP.ZIP

English

Product Environmental Compliance

TE Material Declaration

MD_1734366-4_011620152312_dmtec

PDF

English

FEATURES



Please review product documents or [contact us](#) for the latest agency approval information.

Please Note: Use the Product Drawing for all design activity.

Product Type Features

USB Type A

USB Version 2.0

Size Standard

Connector Style Receptacle

Orientation Vertical

Connector & Contact Terminates To Printed Circuit Board

LED Without

Product Type Connector

Configuration Features

Number of Ports 1

Number of Positions 4

Panel Ground Without

Body Features

Shell Plating Finish Bright

Shell Plating Material Tin

Contact Features

Contact Mating Area Plating Thickness (µm) .76

Contact Mating Area Plating Material Gold Flash over Palladium Nickel

Termination Features

Termination Method Solder

Contact Termination Type Through Hole

Mechanical Attachment

Locating Posts Without
Mounting Location Top
Locking Feature Without
PCB Mount Retention Type Kinked Legs

Housing Features

Housing Color Black
Housing Material Thermoplastic

Dimensions

Tail Length 2.8 mm [.11 in]

Operation/Application

Pick and Place None

Industry Standards

Industry Standard USB 2.0

Packaging Features

Packaging Method Box & Tray, Tray
Packaging Quantity 120

PRODUCT COMPLIANCE



Statement of Compliance

Statement of Compliance

PDF
