


Female Terminal




T-DS1073-S C 6 0 0 ⑥

Contact Plating
6: Tin


Female Terminal

Wire Range		O.D of Wire
Section area mm ²	AWG#	mm
0.33~0.83	22~18	1.7~3.0

Female Housing





N=No. of contacts




I-DS1073-S C W 0 X ⑥

No. of contact
02~13


V/T Type



Right Angle



N=No. of contacts



REV.	DESCRIPTION	DRAWN	CHECKED	APPROVED
A	NEW RELEASE	HP 29/06/05	~	LJC 29/06/05
B	ADD P/N CODE ⑥	JLZ 01/30/15'	~	LJC 01/30/15'
C	DRAWING UPDATE	JLZ 12/27/16'	~	

NOTES:

1. MAIN SPECIFICATIONS

- . Housing material: NYLON 66
- . Wire range: AWG#22~#18
- . Rated voltage: 250V
- . Rated current: 7A
- . Contact resistance: ≤ 30mΩ
- . Insulation resistance: ≥ 1000MΩ
- . Withstanding voltage: 1000V, AC 1 minute
- . Temperature range: -25 ~ +85°C
- . Recommend PC board thickness: 1.6mm

2. PRODUCT NUMBER CODE:

DS1073 - X X X X X

Contact Plating
6: Tin
8: Full gold flash

Housing Color
W: White

Mounting type
R: Right Angle
V: V/T type

Connector type
M: Male

No. of contact
2 to 13

Tel: 86-574-63508787

Fax: 86-574-63510817

E-mail: sales@connfly.com

http://www.connfly.com

Add: East Industry Zone KuangYan

Town Civi Ningbo China

P.C: 315333

GENERAL TOLERANCE		ANGLE TOLERANCE		PROJECTION	TITLE
X.	±0.60	X.	±5°	mm	P.C.B CONNECTOR 3.96mm VH
.X	±0.38	.X	±3°	A4	SERIES DS1073
.XX	±0.25	.XX	±2°		
DRAWING TYPE	CUSTOMER		晨翔电子有限公司 CONNFLY CONNFLY ELECTRONIC CO. LTD		
SCALE	1:1	SHEET 1 OF 1			
DRAWING NO.	C-DS1073-XXXXX-C				