

RJI cord 4x2AWG 27/7 overm. Cat6; 10,0m



Image is for illustration purposes only.
Please refer to product description.

Part number:	09 47 474 7121
Description:	RJI cord 4x2AWG 27/ Cat6; 10,0m
RoHS conformity:	Yes
Limiting temperature (flexible), min.:	0 °C
Limiting temperature (flexible), max.:	60 °C
Limiting temperature, min.:	-20 °C
Limiting temperature, max.:	80 °C
Degree of protection acc. to DIN EN 60 529:	IP 20
Cable length:	10 m
Material, cable:	SF/UTP, PUR