



1825910-6 Product Details

[Share](#) | [Print](#) | [Email](#)


1825910-6

TE Internal Number: 1825910-6
✔ Active

[View 3D PDF](#)

Pushbutton Switches

✔ Always EU RoHS/ELV Compliant (Statement of Compliance)

Product Highlights:

- Switch
- Tactile
- Single Pole - Single Throw Configuration (Pole-Throw)
- Contact Rating = 50mA
- Operating Function = Off [On]

[View all Features](#)

[Add to My Part List](#) | [Request Sample](#) | [Find Similar Products](#) | [Buy Product](#)

Quick Links

- ▶ [Check Pricing & Availability](#)
- ▶ [Search for Tooling](#)
- ▶ [Product Feature Selector](#)
- ▶ [Contact Us About This Product](#)

Documentation & Additional Information

Product Drawings:

- [6MM TACT SWITCH, THRU-HOLE HIGH TEMP \(PDF, English\)](#)

Catalog Pages/Data Sheets:

- [SWITCHES_CORE_PROGRAM_CATALOG \(PDF, English\)](#)

Product Specifications:

- None Available

Application Specifications:

- None Available

Instruction Sheets:

- None Available

CAD Files: (CAD Format & Compression Information)

- [2D Drawing \(DXF, Version C\)](#)
- [3D Model \(IGES, Version C\)](#)
- [3D Model \(STEP, Version C\)](#)

[List all Documents](#)

Related Products:

- [Tooling](#)

Product Features (Please use the Product Drawing for all design activity)

Product Type Features:

- Product Type = Switch
- Tactile = Yes
- Series = FSM
- Mount Angle = Vertical
- Termination Type = Printed Circuit
- Actuator Style = Round

Electrical Characteristics:

- Contact Rating = 50mA

Dimensions:

- Actuator Length (mm [in]) = 1.40 [0.055]

Body Features:

- Mount Style = Through-Hole
- Actuator Profile = Extended
- Actuator Color = Black
- Case Material = Nylon
- Actuator Material = PBT

Contact Features:

- Contact Plating = Silver

Housing Features:

- Process Sealed = No
- Low Profile = No

Configuration Features:

- Configuration (Pole-Throw) = Single Pole - Single Throw
- Operating Function = Off [On]
- Ganged = No
- ESD Grounding Terminal = Without
- Number of Actuators = Single
- Illuminated = No
- Dust Proof = No
- Support Bracket = Without
- Snap Action = Without

Industry Standards:

- [RoHS/ELV Compliance](#) = RoHS compliant, ELV compliant
- [Lead Free Solder Processes](#) = Wave solder capable to 240°C, Wave solder capable to 260°C, Wave solder capable to 265°C
- [RoHS/ELV Compliance History](#) = Always was RoHS compliant

Conditions for Usage:

- Temperature Rating = High

Operation/Application:

- Actuator Force (g [oz]) = 160.00 [5.648]

Packaging Features:

- Packaging Method = Loose Piece

Other:

- Brand = Alcoswitch
- Comment = (On) indicates momentary position.

Corporate Information | Quick Links | Customer Support | Keep Me Informed

Corporate Information

- [About TE](#)
- [Investors](#)
- [News Room](#)
- [Supplier Portal](#)
- [Careers](#)
- [Terms & Conditions](#)
- [Privacy Policy](#)

Quick Links

- [Check Distributor Inventory](#)
- [Cross Reference Products](#)
- [Find Documents & Drawings](#)
- [Product Compliance Support Center](#)
- [Site Map](#)

Customer Support

- [Email or Chat With Us](#)
- [Find a Phone Number](#)
- [Search Knowledge Base](#)
- [Manage Your Account](#)

Keep Me Informed

Receive TE News, Events & Technology Updates

