

Datasheet


RS PRO M12 Female Rear Panel Mount 12 Pin Connector


Part No: 2017186



Technical Specifications:

Rated Operational Voltage	30 V
Current Rating	1.5 A
Insulation Resistance	$\geq 100 \text{ M}\Omega$
Temperature Range	-25° ... +75°C
Coding	A-Coded
Degree of Protection	IP67
Housing Material	Brass Ni Plated
Contact	Cu-Zn
Contact Plating	Gold Flash
Contact Carrier	Nylon 66
O-ring	Neoprene
Pole	12
Clamp Nut	M16 x 1.5





Quality Standard: IEC 61076-2-101



Type Approved
Safety
Regular Production
Surveillance



www.tuv.com
ID 111210483

