







Rev.	ECN Number	Description	Date	Drawn	Checked	Approved

技术要求:

1. 材质: 不锈钢 SUS301, T=0.10±0.005;
2. 端子锡脚焊接面和接触面不可有毛边, 其他部位毛边最大0.03mm;
3. 扭曲: 4.5°/1000mm, 拱形 5mm/1000mm;
4. 标示有“▼”符号的为重点控制和检验尺寸;
5. 未标注之R MAX R0.13;
6. 电镀须满足48小时盐雾测试;
7. 寿命测试>2万次, 产品弹力要求在60gf~80gf之间
8. 镀底50~80U“min”, 产品外表面镀全1U“MIN



焊接尺寸

尺寸公差 ±0.05

		GENERAL TOLERANCE XX. ±0.50 X. ±0.35 .X ±0.25 .XX ±0.15		SCALE: 1:1 UNIT: mm SIZE: A4		DRAWN: _____ CHECK: _____ APPROVE: _____		DATE: _____ DATE: _____ DATE: _____		DWG. NO. 681-0036A-2 PARTS NO. (INTENDED USE) BW0036AG-L3.5W1.0H1.4		TITLE <b>客户图</b> RF Antenna Spring, SMT, L3.50*W1.0*H1.4mm		REV. A SHEET 1/1	
--	--	---	--	------------------------------------	--	--	--	---	--	--	--	---	--	---------------------	--

深圳市蝙蝠无线科技有限公司  
Shenzhen bats wireless co., LTD