

## 4-in-1 USB-C Multiport Video Adapter - Aluminum - 4K 30Hz - Space Gray

Product ID: CDPVDHMDPSG



This space gray USB-C™ multiport video adapter offers a portable solution for connecting your USB Type-C laptop to a VGA, DVI, HDMI® or Mini DisplayPort display. The adapter is also available in [silver \(CDPVGDVHMDMP\)](#) and [rose gold \(CDPVDHMDPRG\)](#).



## All-in-One Video Connectivity with Travel in Mind

Avoid the hassle of carrying different adapters for different displays with this 4-in-1 USB-C adapter. With VGA, DVI, HDMI and mDP output, you can connect your laptop to virtually any display, a convenient plug-and-play solution for travel or Bring Your Own Device (BYOD) applications.



## Astonishing Picture Quality

The HDMI and mDP outputs on this USB-C video adapter support UHD 4K resolutions, providing four times the picture quality of high-definition 1080p. All of the outputs (HDMI, mDP, VGA, DVI) can support high-definition resolutions of up to 1920 x 1200.

## Stylish Connectivity

The USB Type-C adapter has an aluminum housing designed to match your space gray MacBook and is compatible with any device that supports USB-C DP Alt Mode. Featuring a built-in USB-C cable with magnetic cable manager, the USB-C video adapter conveniently stores away for easy travel.

The CDPVDHMDPSG is backed by a StarTech.com 3-year warranty and free lifetime technical support.



### Certifications, Reports and Compatibility



### Applications

- Connect to virtually any display while traveling
- Connect your BYOD MacBook to a VGA, DVI, HDMI or mDP display at work or school
- Connect a secondary VGA, DVI, HDMI or mDP monitor to your MacBook

### Features

- Maximize your video compatibility with a 4-in-1 adapter: USB-C to VGA, DVI, HDMI or Mini DisplayPort
- Get astonishing picture quality with support for UHD resolutions up to 4K 30Hz
- Make the perfect connection, with a USB-C adapter that exactly matches your space gray MacBook
- Maximum portability with built-in magnetic cable manager and a durable aluminum housing

<b>Hardware</b>	Warranty	3 Years
	Active or Passive Adapter	Active
	Adapter Style	Adapters
	AV Input	USB Type-C
	AV Output	DVI HDMI VGA Mini-DisplayPort
	Chipset ID	Cypress - CYPD1120 Cypress - CY7C65210 Parade - PS8348B Parade - PS171
<b>Performance</b>	Audio Specifications	HDMI and mDP output - 7.1 surround sound
	Maximum Analog Resolutions	1920 x 1200 @ 60Hz
	Maximum Digital Resolutions	3840 x 2160 @ 30Hz
	Supported Resolutions	<b>Max HDMI output:</b> 3840 x 2160 @ 30Hz <b>Max mDP output:</b> 3840 x 2160 @ 60Hz <b>HDMI and mDP output:</b> 3840 x 2160, 2560 x 1600, 1920 x 1200, 1920 x 1080, 1280 x 720 <b>DVI and VGA output:</b> 1920 x 1200, 1920 x 1080, 1280 x 720
	Video Revision	DisplayPort 1.2
	Wide Screen Supported	Yes
<b>Connector(s)</b>	Connector A	1 - USB-C (24 pin) DisplayPort Alt Mode Male Input
	Connector B	1 - Mini-DisplayPort (20 pin) Female Output 1 - VGA (15 pin, High Density D-Sub) Female Output 1 - DVI-D (25 pin) Female Output 1 - HDMI (19 pin) Female Output
<b>Special Notes / Requirements</b>	<b>Note</b>	Only one video output is supported on the video adapter at a time, if multiple connections are made, only one of the outputs will function
<b>Environmental</b>	Humidity	<b>Storage:</b> 5% ~ 90 % RH (no condensation) <b>Operating:</b> 10% ~ 85 % RH (no condensation)
	Operating Temperature	0°C to 45°C (32°F to 113°F)

	Storage Temperature	-10°C to 70°C (14°F to 158°F)
<b>Physical Characteristics</b>	Cable Length	110 mm [4.3 in]
	Color	Space Gray
	Enclosure Type	Aluminum
	Product Height	3 cm [1.2 in]
	Product Length	17.5 cm [6.9 in]
	Product Width	14.5 cm [5.7 in]
	Weight of Product	180 g [6.4 oz]
<b>Packaging Information</b>	Package Height	16 mm [0.6 in]
	Package Length	55 mm [2.2 in]
	Package Width	10.5 cm [4.1 in]
	Shipping (Package) Weight	0.1 kg [0.3 lb]
<b>What's in the Box</b>	Included in Package	1 - travel A/V adapter

Product appearance and specifications are subject to change without notice.