

# Han 10B HOOD SE LC M25



Part number	19 30 010 1521
Specification	Han 10B HOOD SE LC M25
HARTING eCatalogue	https://b2b.harting.com/19300101521

Image is for illustration purposes only. Please refer to product description.

#### Identification

Category	Hoods/Housings
Series of hoods/housings	Han <sup>®</sup> B
Type of hood/housing	Hood
Туре	Low construction

#### Version

Locking type	Double locking lever
Size	10 B
Version	Side entry
Cable entry	1x M25
Field of application	Standard hoods/housings for industrial connectors

## Technical characteristics

Limiting temperature	-40 +125 °C
	IP65
Degree of protection acc. to IEC 60529	IP66
	IP67
Type rating acc. to UL 50 / UL 50E	4
	4X
	12

# Material properties

Material (hood/housing)	Aluminium die-cast
Surface (hood/housing)	Powder-coated



# Material properties

Colour (hood/housing)	RAL 7037 (dust grey)
RoHS	compliant
ELV status	compliant
China RoHS	e
REACH Annex XVII substances	No
REACH ANNEX XIV substances	No
REACH SVHC substances	No

## Specifications and approvals

Approvals	DNV GL
UL / CSA	UL 1977 ECBT2.E235076 CSA-C22.2 No. 182.3 ECBT8.E235076
CE	Yes

## Commercial data

Packaging size	1
Net weight	141.5 g
Country of origin	Germany
European customs tariff number	85389099
eCl@ss	27440202 Shell for industrial connectors