stanleytools.co.uk stanleytools.co.uk

FATMAX® FLOORING SAW



- 7 teeth per inch for a fine finish
 Induction hardened teeth stay sharper twice as long than previous model
 - 3 sided precision ground teeth offer razor sharp cutting edges at every stage of the stroke
 - Finger rest, ergonomic design, useful for extra control when starting a cut
 - Anti-friction coating ideal for laminated floors, paneling, skirting boards and jointing strips
 - Bi-material handle screwed and ultrasonically welded for comfort and security
 - Handle with marked 45° and 90° angles

STANLEY	Description	<u></u>		
1-20-180	450mm / 18" FatMax® Flooring Saw 7 teeth per inch	Sleeve	4	3253561201806

FATMAX® 22" PLASTERBOARD SAW



- Specially designed tooth geometry ideal for plasterboard, plaster tiles, corrugated partitions
 - Bi-material handle screwed and ultrasonically welded for comfort and security
 - 3 sided precision ground teeth offer razor sharp cutting edges at every stage of the stroke
 - Induction hardened teeth stay sharper twice as long than previous model
 - Handle with marked 45° and 90° angles

STANLEY	Description	٥		
2-20-037	550mm / 22" FatMax® Plasterboard Saw 7 teeth per inch	Sleeve	6	3253562200372

FATMAX® FOLDING JAB SAW



- **STANLEY**. 8 teeth per inch ideal to cut through plasterboard
- Triple bevelled toothing for 50% guicker, easier cutting
 - Secure locking mechanisms in 3 positions (90°, 135°, 180°) for maximum flexibility and increased leverage for corner and ceiling cuts
 - Soft grip handle for added comfort
 - Fold away blade storage for safety

STANLEY	Description	<u>©</u>		
FMHT0-20559	FatMax® Folding Jabsaw	Carded	6	3253560205591

FATMAX® PLASTERBOARD/JAB SAW

• 7 teeth per inch • Ideal for punching through plasterboard

- Anti-slip ergonomic bi-material handle for optimum user comfort
- Triple bevelled toothing for 50% quicker easier cutting
- Sharp point for piercing board

STANLEY	Description	<u></u>		
0-20-556	150mm/6" FatMax® Jab Saw 7 teeth per inch	Carded	6	3253560205560
7-20-556	150mm/6" FatMax® Jab Saw plus Scabbard 7 teeth per inch	Merchandiser of 10	10	3253567205563

PLASTERBOARD/JAB SAW

- **STANLEY** 7 teeth per inch ideal for punching through plasterboard
 - Soft grip handle for ease of use

STANLEY	Description	٥		
0-15-556	150mm/6" Plasterboard Saw 7 teeth per inch	Loose	6	3253560155568

3 IN 1 SAW

- **STANLEY**. Multi-Purpose 3-in-1 Saw Set offers 3 different blades in one space saving design
 - universal pull saw blade, metal saw blade and compass saw blade
 - Anti-slip ergonomic bi-material handle for optimum user comfort
 - The turn knob allows blades to be easily changed and they can be tilted into 6 different positions
 - The main blade utilises a pull saw tooth configuration which is less likely to jam or bend while in use
 - 250mm / 10" aggressive tooth 11 teeth per inch universal wood saw blade cuts on the "pull" stroke – perfect for general woodwork and pruning
 - 200mm / 8" compass saw blade 9 teeth per inch for more detailed work
 - 150mm / 6" metal hacksaw blade 24 teeth per inch for cutting metal pipes and rods

STANLEY	Description			
0-20-092	3 in 1 Saw	Carded	2	3253560200923

FATMAX® 10" REVERSIBLE FLUSH CUT SAW



- Spring-loaded pin allows blade to be reversed to cut from left or right position
 - Steel back prevents bending for strong, true, straight cuts
 - Wide blade for precise cutting such as dovetails, small joints and cut-offs
 - Reversible handle provides improved access in close quarters
 - New soft grip handle for comfort and support

video can be viewed v.stanleytools.co.uk

STANLEY	Description	<u></u>		
0-15-252	10" FatMax® Reversible Flush Cut Saw	Carded	8	3253560152529

