

- Quick Links
- Cross reference
- RoHS/LF P/N Search
- Industry Standards
- Alphabetical List
- Documentation
- 3D model search
- Customer drawing search
- Multi Selection Search
- Search by category

Start > Search=10127716-16LF* > 10127716-16LF

10127716-16LF
10127716-16LF - Minitek® Pwr 3.0 : Minitek® Pwr 3.0
Receptacle Housing, Dual row, 16 positions Glow Wire
Compatible



ACTIVE 48

RoHS Compliant

Distributor Stock

CORE RANGE

Print Datasheet

FCI Brings You More

- Contact our sales/technical support
- Sample request

- Customer drawing
- Product Environmental Compliance Report

Specifications Download document

General Dimensional Electrical Mechanical Physical Approvals / Certifications Other Features

General	
Number of contacts	16
Series	10127716
Dimensional	
Pitch	3.0
Electrical	
Withstanding Voltage	1000 VAC
Current rating	Up to 5 Amps
Resistance (Contact)	20 milliohm max. final 10 milliohm max. initial
Resistance (Insulation)	1000MΩ min
Voltage rating	250V
Mechanical	
Durability (Mating cycles)	100 Cycles
Insertion force	4.5N max
Withdrawal Force	2N min before durability, 1.5N min after durability
Glow Wire Compatible	Yes
Physical	
Color (Housing)	Black
Material (Housing)	High Temperature Thermoplastic
Temperature (Range)	-40°C to +105°C
Approvals / Certifications	
Approvals / Certifications	UL Approved
UL File Number	ML E467317
Other Features	
Packaging (Type)	PE Bag

Disclaimer : The information above is for reference only. For more technical details, refer to product specification and application specification.