



ITEM-NO. (ITEM-NO.)	714-102
Cross section1 (Cross section / mm²)	0.2 - 1.5
Cross section2 (Cross section / AWG)	24 - 16
Strip length (Strip length / mm)	10
Measured voltage (Measured voltage / V)	160
Measured shock voltage (Measured shock voltage / kV)	2.5
Pollution degree (Pollution degree)	2
Current intensity (Current intensity / A)	8
RM (PIN SPACING / mm)	3.5
P (NO. OF POLES)	2
Height (Height / mm)	23
Width (Width / mm)	7.7
Depth (Depth / mm)	7.8
No. of connection Points (No. of connection Points)	2
No. of potentials (No. of potentials)	2
COLOR (COLOR)	schwarz
Comment (Comment)	L = (No. of poles - 1) x Pin Spacing + 4.2 mm