


THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.



PANDUIT PART NO.	BUNDLE DIA.		A in (mm)	B in (mm)	C in (mm)	D in (mm)	E in (mm)	F in (mm)	MIN. LOOP TENSILE lbs. (N)	CROSS SECTION	WEIGHT 100 pcs lbs (g)
	MIN. in (mm)	MAX. in (mm)									
SG200S	.06 (1.5)	2.0 (51)	.046 (1.2)	.225 (5.7)	.290 (7.4)	.220 (5.6)	.342 (8.7)	8.3 (210.8)	50 (222)	STANDARD	.30 (137)
SG250S	.16 (4.1)	2.6 (66)	.050 (1.3)	.225 (5.7)	.318 (8.1)	.220 (5.6)	.360 (9.1)	10.4 (264.2)	75 (334)	STANDARD	.41 (186)
SG300S	.16 (4.1)	3.2 (81)	.050 (1.3)	.225 (5.7)	.318 (8.1)	.220 (5.6)	.360 (9.1)	12.4 (315.0)	75 (334)	STANDARD	.49 (220)
SG370S	.16 (4.1)	4.2 (107)	.052 (1.3)	.225 (5.7)	.330 (8.4)	.220 (5.6)	.360 (9.1)	15.3 (388.6)	75 (334)	STANDARD	.61 (278)

**NOTE:**

1) SEE CURRENT PRICE SHEET FOR PART NUMBER SUFFIX DESIGNATION FOR PACKAGE SIZE & PART COLOR.

										DIMENSIONS IN PARENTHESIS ARE IN METRIC UNITS				
										<b>PANDUIT</b> CORP. TINLEY PARK, ILLINOIS				
										SUPER-GRIP CABLE TIES				
										UNLESS OTHERWISE SPECIFIED, DIMENSIONAL TOLERANCES ARE: (.X) ± (.XXX) ± .020(.5) (.XX) ±.02(.5) ANGLES ±		UNLESS OTHERWISE SPECIFIED, ALL DIMENSIONS ARE GIVEN IN INCHES, THIRD ANGLE PROJECTION.		
										DRAWN BY JABO MAT'L:		SCALE NONE		
										DATE 4/28/05		DRAWING NO. SS-27441		DWG A
										CHK'D BOBK		NYLON 6.6		SIZE
2	9/19/07	JABO		SG250S, SG300S, SG370S TENSILE WAS 70, NOW 75 LBS.				27441	2			SHEET 2 OF 3		
REV	DATE	BY	CHK	DESCRIPTION				ECN	R	CUST	SUP			

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Panduit:](#)

[SG300S-M](#) [SG300S-M0](#) [SG200S-M0](#) [SG200S-M](#) [SG250S-C0](#)