



PART No.	THREAD A	NOMINAL DIMENSIONS (mm)						WEIGHT gms.
		B	C	D	E	F	G	
AL10/M12/A	M12x1.5	10.0	25.0	16.1	7.5	15.2	12.5	3
AL13/M16/A	M16x1.5	11.5	33.0	21.3	11.6	19.0	17.0	5
AL16/M16/A	M16x1.5	11.5	33.0	23.7	11.6	23.7	19.8	6
AL16/M20/A	M20x1.5	11.5	33.0	23.7	15.3	23.4	19.8	7
AL18/M20/A	M20x1.5	11.5	34.0	26.3	15.0	23.0	21.6	7
AL20/M20/A	M20x1.5	13.0	34.8	28.1	14.8	26.8	21.7	9
AL21/M20/A	M20x1.5	14.0	34.7	28.9	14.8	26.7	25.0	9
AL21/M25/A	M25x1.5	11.0	35.75	29.0	17.8	31.5	25.0	10
AL25/M25/A	M25x1.5	16.0	35.9	32.8	20.0	30.8	28.7	12
AL28/M25/A	M25x1.5	16.2	36.8	36.8	20.0	35.5	32.3	14
AL28/M32/A	M32x1.5	12.2	37.1	36.8	22.3	37.7	32.5	17
AL34/M32/A	M32x1.5	16.0	37.8	43.2	26.5	41.5	38.9	20
AL34/M40/A	M40x1.5	12.1	37.9	43.0	30.3	45.3	39.0	23
AL42/M40/A	M40x1.5	16.0	47.8	53.8	31.0	52.8	49.5	45
AL42/M50/A	M50x1.5	12.1	48.1	54.0	37.8	66.8	50.0	57
AL54/M50/A	M50x1.5	16.0	53.0	66.9	40.2	67.2	62.6	71
AL54/M63/A	M63x1.5	16.0	53.0	66.9	50.0	70.0	62.6	75

MATERIAL POLYAMIDE 6,6
 SELF EXTINGUISHING UL94 V2
 HALOGEN, CADMIUM, PHOSPHOR AND SULPHUR FREE
 EXCELLENT IMPACT RESISTANCE
 IP 66 RATING – USE ASL SEAL FOR HIGHER IP
 REQUIREMENTS (SEE CHART No 097)



BIRMINGHAM ENGLAND

This drawing/document is a COPYRIGHT and the property ADAPTAFLEX LIMITED It must not be copied (in whole or part) used for manufacture or otherwise disclosed without prior written consent of the company. The Company's policy is one of continuous improvement and it therefore reserves the right to change specifications at any time without notice.

MATERIAL **NYLON 66 (PA66)**

FINISH **FINE SPARK**

COLOUR **BLACK**

DATE **21/8/02**

CHARTS. 002

TITLE

**ADAPTALOK
 METRIC THREADS
 DATA SHEET**