

Purchase items directly from TE.com

2273011-1

M8 x 1.0 Angled socket Pigtail



TE Internal #: **2273011-1**
 TE Internal Description: **M8 x 1.0 Angled socket Pigtail**
[All M8 FEMALE R/A PIGTAIL \(16\)](#)

Connector Type : **Receptacle**
 Number of Positions : **4**
 Keying : **A**
 Housing Material : **Plastic**
 Cable Assembly Type : **M8 Pigtail**

[Compatible Parts & Tooling](#)

We are here to help!

Get in touch with our product experts.



[CHAT WITH US](#)



[EMAIL US](#)



[CALL US](#)

Documents

Features

Product Compliance

Product Description

Our M8 Female Right Angle Pigtails are offered in 3,4 positions, PUR/PVC, Shielded and non-shielded cables, up to 10m length.

[View All M8 FEMALE R/A PIGTAIL \(16\)](#)

Product Drawings

M8 x 1.0 Angled socket Pigtail
[M8 X 1.0 Angled Socket Pigtail](#) English

Datasheets & Catalog Pages

M8 / M12 Connector System Catalog
[ENG_CS_1-1773701-8_M8M12_CONNECTOR_SYSTEM_1906.pdf](#) English
[ENG_DS_1-1773966-2_0119.pdf](#) English

Product Description

Our M8 Female Right Angle Pigtails are offered in 3,4 positions, PUR/PVC, Shielded and non-shielded cables, up to 10m length.

[View All M8 FEMALE R/A PIGTAIL \(16\)](#)

Please review product documents or [contact us](#) for the latest agency approval information. Please Note: Use the Product Drawing for all design activity.

Product Type
Features

Assembly Type : **Pigtail**
Connector Type : **Receptacle**
Cable Assembly Type : **M8 Pigtail**
Shielded : **No**

Configuration
Features

Number of Positions : **4**
Keying : **A**
Configuration : **Single Ended**

Body Features

Cable Jacket Color : **Black**

Mechanical
Attachment

Screw & Hole Thread Size : **M8**
Mounting Angle : **Right Angle**

Housing Features

Housing Material : **Plastic**

Dimensions

Wire Size (mm²): **.326**
Wire Size (AWG): **22**
Cable Assembly Length (mm): **1500**

Usage Conditions

Operating Temperature Range : **-40 – 80 °C [-40 – 176 °F]**



[ABOUT TE CONNECTIVITY](#)

[FOR PARTNERS](#)

[SUPPORT](#)

[CALL US](#)

[LIVE CHAT](#)

[UNITED STATES \(EN\)](#)