




THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.

PART NUMBER	PRINT-ON HEIGHT "A" inches [mm] +/- .031	WIDTH "B" inches [mm] +/- .031	"C" LENGTH	MARKERS PER CARDS	STD. PKG. CARDS	STD. CTN. CARDS
PSWMH-375Y	.375 [9.5]	.375 [9.5]	.75 [19.1]	50	25	100
PSWMH-750Y	.375 [9.5]	.75 [19.1]	.75 [19.1]	24	25	100

NOTES:

1. MILLIMETER ARE IN [ ].
2. 25 CARDS PER BOX.



CAD FILENAME/LAYERS 100295FE-DC-C10633/01B

REV	DATE	BY	CHK	DESCRIPTION	ECN	R	CUST	SUP
1	3/29/11	RVU		UPDATE ON TABLE, CHG. FROM B SIZE TO A SIZE. UPDATE TOL. AND MATERIAL.	6337	R		
0	1/9/08	RVU		DRAWING RELEASE	5261	R		

PANDUIT CORP. TINLEY PARK, ILLINOIS

CUSTOMER DRAWING  
SELF-LAM. WIRE MARKER CARDS  
PSWMH-\*\*\*Y

UNLESS OTHERWISE SPECIFIED, DIMENSIONAL TOLERANCES ARE:  
 (.X) ± .12 (.XXX) ± .025  
 (.XX) ± .062 ANGLES ±

UNLESS OTHERWISE SPECIFIED, ALL DIMENSIONS ARE GIVEN IN INCHES, THIRD ANGLE PROJECTION.

DRAWN BY RVU  
DATE 1/9/08  
CHK'D

MAT'L: GMV3 SELF-LAM. VINYL

SCALE NTS  
DRAWING NO. C10633  
DWG SIZE A

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

## Panduit:

[PCMH-23](#) [PCMH-1](#) [PCMH-5](#) [PCMH-9](#) [PCMH-12](#) [PCMH-2](#) [PCMH-20](#) [PCMH-15](#) [PCMH-3](#) [PCMH-21](#) [PCMH-18](#)  
[PCMH-19](#) [PCMH-17](#) [PCMH-0](#) [PCMH-8](#) [PCMH-7](#) [PCMH-25](#) [PCMH-22](#) [PCMH-11](#) [PCMH-4](#) [PCMH-16](#) [PCMH-6](#)  
[PCMH-13](#) [PCMH-10](#) [PSWMH-750Y](#) [PCMH-14](#) [PCMH-24](#)