



Notes:

1. Material and Finish:
 - Receptacle Housing: Polyester (Black); UL94 V-0
 - Panel Nut: Brass, Finish: Nickel Plated
 - Panel Gasket: Silicone, Color: White
 - Duplex LC Adaptor Assembly:
 - Housing: Mod. PPO, UL94 V-0, Color: **SM Blue/MM Beige/APC SM Green** (b)
 - Alignment Sleeves: SM Ceramic/MM Phosphor Bronze
 - Dust Cap: PP, Color: Neutral transparent
 - Operating Temperature: -40~C to +85~C
2. Connector can be front or rear mounted to a maximum panel thickness of 3.2mm.
3. IP67 rated when covered or fully mated with the appropriate mating connector
- (d) 4. Recommended Mounting Panel Nut torque is 20 to 25 lb-inch

Description	Part Number
Single Mode (SM)	17-300010
Multi Mode (MM)	17-300020
(c) APC Single Mode (APC SM)	17-300170

Directive 2002/95/EC RoHS Compliant

THIS DRAWING MAY NOT BE COPIED OR REPRODUCED IN ANY MANNER AND MAY NOT BE PASSED ON TO A THIRD PARTY WITHOUT WRITTEN PERMISSION. OWNERSHIP AND COPYRIGHT OF CONEC CORPORATION. DO NOT ALTER CAD DRAWING BY HAND	Customer:			Tolerance Unless otherwise specified 0 PLC ±0.50 1 PLC ±0.38 2 PLC ±0.25 3 PLC ±0.10 ANGLES ±.7		Scale: 1.5:1	Dim. in mm		
	Name	Title	Approval Date			Autodesk Inventor	Material: See Notes		
						2008	Date	Name	Title: IP67 Industrial Duplex LC Receptacle Assembly Kit Plastic Version
						Draw.	Jun. 06	Vincent Ke	
						Appd.	Jun. 06	J. Chaudry	
d	3 x d	Sep/25/2013	Vincent Ke	Norm		Drawing No.: 17K1A002 Part No.: SEE PART NUMBER TABLE			
c	3 x c	Feb/25/2011	Vincent ke	D-old					
b	1 x b	May/28/2009	Vincent Ke						
a	original								
Rev.	Changes	Date	Name			DIN A3			
						Sheet 1/1			

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[CONEC:](#)

[17-300010](#) [17-300020](#)