

FEATURES

- Measures max., min., and average values in both metric and imperial units
- Clear and easy to read LCD display with a memory function
- Supplied with a selection of accessories
- Calibration Certificate (supplied with a calibrated versions only)

RS PRO Tachometer, Best Accuracy $\pm 0.02\%$ Contact, Non Contact LCD 99999rpm

RS Stock No.: 845-9674



RS Professionally Approved Products bring to you professional quality parts across all product categories. Our product range has been tested by engineers and provides a comparable quality to the leading brands without paying a premium price.

Product Description

This professional tachometer (digital rotary measuring instrument) from RS PRO offers the latest technologies in a robust and durable housing and allows for fast and accurate measurements of rotational and linear speeds. It can be used as both an optical tachometer to measure rotations and also a contact tachometer reader to measure rotational speed, RPM, linear speed and distance. The ergonomically designed body makes it a comfortable device to use at any location.

General Specifications

Category	Contact ,Non-Contact
Maximum Speed	99999rpm
Minimum Speed	0rpm
Display Type	LCD
Application	Motors, Turbines, Fans, Wheel, Shafts, Rollers

Electrical Specifications

Battery Type	AA
---------------------	----

Mechanical Specifications

Dimensions	170mm x 70mm x 40mm
Height	40mm
Length	170mm
Width	70mm
Weight	250g

Operation Environment Specifications

Operating Temperature	0°C to 50°C (32°F to 122°F)
Maximum Operating Temperature	50°C
Minimum Operating Temperature	0°C

