

Features

- This valve is designed for a working pressure of 700 bar.
- All oil inlet holes are 3/8"-NPT conical thread to guarantee a perfect connection without oil leakage.

RS PRO Hydraulic Fittings

RS Stock No.: 235-8211



RS PRO Professionally Approved Products bring to you professional quality parts across all product categories. Our product range has been tested by engineers and provides a comparable quality to the leading brands without paying a premium price.

Product Description

The RS PRO Hydraulic Fittings – Regulates the flow rate of both outlets independently, and can even block the flow. Can also be used to protect pressure gauges.

Five 3/8" – NPT hydraulic couplers can be connected to this valve.

General Specifications

Hydraulic Fitting Type	Hydraulic Valve
Material	Steel F-1150
Colour	Black
Finish	Nitrated
Shape	Squared
Type of Sealing	None
With Drain	No
Applications	Hydraulic System Installation, Flow Control

Mechanical Specifications

Maximum Operating Pressure	700 bar
Length	148 mm
Width w/ Lever	95 mm
Width	40 mm
N.° of Outlets	5

Diameters:

Thread Standard	NPT
Thread Size	3/8" - NPT
Gender	Female

