

## Features

- Capacity: 22 Ton
- Stroke: 16 mm
- Low profile, for use in confined spaces.
- With two parallel sides to work in horizontal position.
- With through holes for easy fixing.
- Nitrided to improve corrosion and wear resistance.
- With chrome-plated plunger and scraper to extend cylinder life.
- Optional tilting saddle.

## RS PRO Hydraulic Cylinders

RS Stock No.: 235-8254



RS PRO Professionally Approved Products bring to you professional quality parts across all product categories. Our product range has been tested by engineers and provides a comparable quality to the leading brands without paying a premium price.

## Product Description

The RS PRO low profile cylinders, for applications in confined spaces: movement of machines, clamping of tools.

The single acting hydraulic cylinders have only one female quick coupler.

If the coupler has to be installed on the cylinder, apply Teflon around the 3/8" NPT male thread of the coupler.

## General Specifications

Cylinder Type	Nitrided Steel, Solid Plunger, Spring Return
Single/Double Acting	Single Acting
Capacity	22 Ton
Stroke	11 mm
Cylinder Effective Area	33 cm <sup>2</sup>
Oil Capacity	37 cm <sup>2</sup>
Body Material	Nitrided Steel
Saddle Type	Standard Plain
Handles	No
Applications	Low profile applications such as machine movement, fixture clamping, load testing...

## Mechanical Specifications

Maximum Operating Pressure	700 bar - 10150 psi
Closed Height	52 mm
Extended Height	63 mm
Weight	2.8 kg
Distance From Fixing Holes To Plunger	39 mm
Distance From Plunger To Cylinder Back	41 mm
Fixing Holes Distance	50 mm
Cylinder Width	80 mm

### Diameters:

Cylinder Bore	65 mm
Plunger	57 mm
Fixing Holes	9 mm

## Approvals

Compliance/ Standards

CE, UKCA

