




CONNECTORS

WIRE-TO-BOARD CONNECTOR CONTACTS



✓ Active

TE CONNECTIVITY (TE)

MOD II COSI RECP CONT STR PH-B

AMPMODU | AMPMODU IV/V

280530-1

TE Internal Number: 280530-1

Alias ID: A12439-000, AMP-0-0280530-1

EU RoHS Compliant

EU ELV Compliant

Contact Type Socket

Wire/Cable Size (AWG) 26 – 22

Wire/Cable Size (mm²) .12 – .4

Contact Mating Area Plating Material Gold

Packaging Method Strip

[↓ PRODUCT DRAWING](#)
English

[↓ 3D PDF](#)

DOCUMENTATION

Product Drawings

AMPMODU II REC. CONTACT, STD PRESSURE, C. O. S. I.

PDF (TIFF AVAILABLE)

English

CAD Files

3D PDF

PDF

3D

Customer View Model

2D_DXF.ZIP

English

Customer View Model

3D_IGS.ZIP

English

Customer View Model

3D_STP.ZIP

English

Product Specifications

Application Specification

AMPMODU Mod.II Interconnection System, Receptacle Contact

PDF

English

Product Environmental Compliance

TE Material Declaration

MD_280530-1_06232014633_dmtec

PDF

English

FEATURES



Please review product documents or [contact us](#) for the latest agency approval information.

Please Note: Use the Product Drawing for all design activity.

Product Type Features

Connector & Contact Terminates To Wire & Cable

Wire/Cable Type Discrete Wire

Product Type Contact

Applied Pressure Standard

With Insulation Support Yes

Contact Features

Contact Type Socket

Contact Mating Area Plating Material Gold

Crimp Area Plating Material Gold Flash

Contact Base Material Phosphor Bronze

Contact Mating Area Plating Thickness (µin) 15

Termination Features

Termination Method to Wire/Cable Crimp

Dimensions

Wire/Cable Size (AWG) 26 – 22

Wire/Cable Size (mm²) .12 – .4

Insulation Diameter .89 – 1.55 mm [.035 – .061 in]

Packaging Features

Packaging Method Strip

Packaging Quantity 10000

PRODUCT COMPLIANCE



Statement of Compliance

Statement of Compliance

PDF
