




CONNECTORS

BOARD-TO-BOARD CONNECTOR HOUSINGS



✓ Active

TE CONNECTIVITY (TE)

AMPMODU MODU I REC HOUSING

AMPMODU

280591

TE Internal Number: 280591

EU RoHS Compliant

EU ELV Compliant

Connector Style Receptacle

Centerline (mm) 3.96

Centerline (Pitch) (in) .156

Number of Positions 4

Number of Rows 1

[↓ PRODUCT DRAWING](#)
English

[↓ 3D PDF](#)

DOCUMENTATION

Product Drawings

AMPMODU I RECEPTACLE HOUSINGS

PDF

English

CAD Files

Customer View Model

3D_IGS.ZIP

English

Customer View Model

3D_STP.ZIP

English

Customer View Model

2D_DXF.ZIP

English

3D PDF

PDF

English

Product Specifications

Product Specification

AMPMODU I Interconn. System, 3.98mm. Pitch

PDF

English

Product Environmental Compliance

TE Material Declaration

MD_280591_09022015167_dmtec

PDF

English

Agency Approvals

Agency Approval Document

AMPMODU CONNECTOR REPORT (GERMANY)

PDF

English

FEATURES



Please review product documents or [contact us](#) for the latest agency approval information.

Please Note: Use the Product Drawing for all design activity.

Product Type Features

Connector Style Receptacle

Profile Standard

Configuration Features

Number of Positions 4

Number of Rows 1

Stamped Yes

Keyed No

Contact Features

Contact Type Socket

Mechanical Attachment

Mounting Ears Without

Mating Alignment Without

Housing Features

Centerline (mm) 3.96

Centerline (Pitch) (in) .156

Housing Material Polycarbonate GFF

Housing Color Green

Industry Standards

UL Flammability Rating UL 94V-1

Statement of Compliance

Statement of Compliance

PDF
