




[+ CABLE ASSEMBLIES](#)

[LIGHTING CABLE ASSEMBLIES](#)



✓ Active

TE CONNECTIVITY (TE)

NECTOR M, SEALED 3P PIN - 3P SKT, UL

NECTOR

2829461-1

TE Internal Number: 2829461-1

[EU RoHS Compliant](#)

[EU ELV Compliant](#)

Product Line NECTOR M

Wire Color Black

Cable Assembly Length 1219.2 mm [48 in]

Voltage Rating (VAC) 600

Connector Type (End A) Plug

[↓ PRODUCT DRAWING](#)
English

DOCUMENTATION

Product Drawings

SEALED 3 POS PIN TO SEALED 3 POS SOCKET, STD UL

PDF

English

Catalog Pages/Data Sheets

5-1773465-6_NECTOR_M

PDF

English

FEATURES

Please review product documents or [contact us](#) for the latest agency approval information.

Please Note: Use the Product Drawing for all design activity.

Product Type Features

Product Line NECTOR M
Connector Type (End A) Plug
Connector Type (End B) Socket
Product Type Cable Assembly
Sealed Yes

Configuration Features

Number of Positions 5
Keyed Yes

Electrical Characteristics

Voltage Rating (VAC) 600
Operating Voltage Reference AC

Body Features

Wire Color Black

Housing Features

Housing Color Black

Dimensions

Cable Assembly Length 1219.2 mm [48 in]

Statement of Compliance

Statement of Compliance

PDF
