

Housing cover - BC 35,6 DKL R KMGY

2896157

<https://www.phoenixcontact.com/us/products/2896157>

Please be informed that the data shown in this PDF document is generated from our Online Catalog. Please find the complete data in the user documentation. Our General Terms of Use for Downloads are valid.

DIN rail housing for use in distribution boards in accordance with DIN 43880, Latching cover (non-detachable), width: 35.6 mm, height: 45 mm, depth: 8 mm, color: light grey (7035)



Your advantages

- Coordinated housing and connection system for faster device development
- Individual online configuration for diverse applications in building automation
- Variety of connection technology
- Can be mounted on the DIN rail or the wall
- With DIN-rail-mountable bus connector and power connector system as an option
- Tool-free mounting
- Available in overall widths from one to nine HP (17.8 mm ... 161.6 mm)
- Compliant with DIN EN 43880

Housing cover - BC 35,6 DKL R KMGY



2896157

<https://www.phoenixcontact.com/us/products/2896157>

Commercial Data

Item number	2896157
Packing unit	1 pc
Minimum order quantity	10 pc
Sales Key	A13
Product Key	ACHBAB
Catalog Page	Page 698 (C-1-2013)
GTIN	4046356096560
Weight per Piece (including packing)	5.95 g
Weight per Piece (excluding packing)	4.47 g
Customs tariff number	85389099
Country of origin	DE

Housing cover - BC 35,6 DKL R KMGY



2896157

<https://www.phoenixcontact.com/us/products/2896157>

Technical Data

Notes

Assembly instruction:	Refer to the data sheet for the range in the download area.
-----------------------	---

Product properties

Product type	Cover
Type	Latching cover (non-detachable)
Housing type	DIN rail housing for use in distribution boards in accordance with DIN 43880
Ventilation openings present	no
Housing series	BC

Dimensions

Width	35.6 mm
Height	45 mm
Depth	8 mm

Material specifications

Color	light grey (7035)
Flammability rating according to UL 94	V0
Surface characteristics	untreated
Housing material	Polycarbonate

Environmental and real-life conditions

Vibration test

Specification	IEC 60068-2-6:2007-12
Frequency	10 - 150 - 10 Hz
Sweep speed	1 octave/min
Amplitude	0.15 mm (10 - 58.1 Hz)
Acceleration	2g (58.1 - 150 Hz)
Test duration per axis	2.5 h
Test directions	X-, Y- and Z-axis

Glow-wire test

Specification	DIN EN 60695-2-11 (VDE 0471-2-11):2014-11
Temperature	850 °C
Time of exposure	30 s

Mechanical strength / tumbling barrel

Specification	IEC 60068-2-31:2008-05
Height of fall	50 cm
Frequency	50

Shocks

Housing cover - BC 35,6 DKL R KMGY



2896157

<https://www.phoenixcontact.com/us/products/2896157>

Specification	IEC 60068-2-27:2008-02
Pulse shape	Half-sine
Acceleration	15g
Shock duration	11 ms
Number of shocks per direction	3
Test directions	X-, Y- and Z-axis (pos. and neg.)

Degree of protection (IP code)

Specification	IEC 60529:1989-11 + AMD 1:1999-11 + AMD 2:2013-08
---------------	---

Ambient conditions

Max. IP code to attain	IP20
Ambient temperature (operation)	-40 °C ... 105 °C (depending on power dissipation)
Ambient temperature (storage/transport)	-40 °C ... 70 °C
Ambient temperature (assembly)	-5 °C ... 100 °C
Relative humidity (storage/transport)	95 %

Mounting

Mounting type	Latching with upper housing part
Mounting position	Vertical (horizontal DIN rail)

Housing cover - BC 35,6 DKL R KMGY



2896157

<https://www.phoenixcontact.com/us/products/2896157>

Approvals



EAC

Approval ID: B.01687



UL Recognized

Approval ID: FILE E 240868

Housing cover - BC 35,6 DKL R KMGY



2896157

<https://www.phoenixcontact.com/us/products/2896157>

Classifications

ECLASS

ECLASS-9.0	27182702
ECLASS-10.0.1	27182702
ECLASS-11.0	27182702

ETIM

ETIM 8.0	EC001031
----------	----------

UNSPSC

UNSPSC 21.0	31261500
-------------	----------

Housing cover - BC 35,6 DKL R KMGY



2896157

<https://www.phoenixcontact.com/us/products/2896157>

Environmental Product Compliance

China RoHS

Environmentally friendly use period: unlimited = EFUP-e

No hazardous substances above threshold values

Housing cover - BC 35,6 DKL R KMGY



2896157

<https://www.phoenixcontact.com/us/products/2896157>

Accessories

Fiber optic

Fiber optic - HS LC-V-D3/ R2XC1-5,08 - 2202311

<https://www.phoenixcontact.com/us/products/2202311>



Light guides, passive, rigid, can be used for the BC housing range (housing must be processed)

Fiber optic

Fiber optic - HS LC-V-D3/ R3XC1-5,08 - 2202312

<https://www.phoenixcontact.com/us/products/2202312>



Light guides, passive, rigid, can be used for the BC housing range (housing must be processed)

Phoenix Contact 2022 © - all rights reserved

<https://www.phoenixcontact.com>

Phoenix Contact USA

586 Fulling Mill Road

Middletown, PA 17057, United States

(+717) 944-1300

info@phoenixcon.com