

HL-5240L

TN3130/ TN3170/ DR3100

Low cost feature packed mono laser printer



### **Copy**

Sometimes it's not easy keeping costs down and the standard of work up. But Brother's HL-5240L makes it look easy, with business quality printing for the home or small office at a price that makes good business sense. Especially with features like 24 pages per minute print speed and up to 800 sheet paper capacity.

### **Catalogue Spec**

- Compact mono printer ideal for the home worker or a small office
- Fast efficient 24 pages per minute printing
- Cost saving separate drum and toner
- High yield toner option offering even more cost effective printing
- Time saving 250 sheet paper capacity
- Boost paper capacity to 800 sheets with optional trays
- 12 months warranty and lifetime technical support

## Detailed Spec

### General

Engine	Laser
Speed	Up to 24 ppm (pages per minute)
Resolution	HQ1200 (1,200 x 1,200dpi), 600dpi, 300dpi
Interface	Hi-Speed USB 2.0 & IEEE Parallel 1284
Memory	16MB (Expandable up to 528MB, using industry standard 1 DIMM (144 PIN) slot)
Lower Paper Tray Capacity	Up to 250 sheets**
Multi-purpose Paper Tray Capacity	50 sheets**
Optional Lower Paper Tray Capacity	Up to 250 sheets**
Total Paper Input Capacity	800 sheets**
Output Paper Capacity	Up to 150 sheets (face down)**
Emulation	PCL®6, BR-Script3, IBM® ProPrinter XL, Epson® FX-850
Resident Fonts	PCL®6: 66 Scalable Fonts, 12 Bitmap Fonts, 11 Barcodes BR-Script 3: 66 scalable fonts
CPU Speed	266MHz (VR5500)
On / Off Switch	Yes

### Control Panel

LED Display	4 Toner/Drum/Paper LED and 3-colour Status LED
Buttons	There are two buttons, Job Cancel and "Go".

### Printer Driver

Windows®	Windows Vista®, Windows® XP Professional (32 & 64 bit editions) / XP Home Edition, Windows Server 2003® (32 & 64 bit editions), Windows® 2000 Professional, Windows NT®4.0 / Me / 98(SE) / 98 and 95
Macintosh®	Brother Laser Driver for Mac OS® 9.1 - 9.2, Mac OS® X 10.2.4 or greater
Linux	Printer Driver for Linux***

### Printer Driver Functions

N-up Printing	Reduce up to 2, 4, 9, 16 or 25 A4 pages to 1 A4 page
Poster Printing	Enlarge 1 A4 page into a poster using 4, 9, 16 or 25 A4 pages
Watermark Printing †	Watermark your documents with predefined text or with your own user-defined messages
Quick Print Set-up †	Allows users to quickly select print options in the driver
Status Monitor †	A function for showing printer errors on your PC
Manual Duplex	Manually print on both sides of the paper

### Media Specifications

Media Types	Standard paper tray - Plain paper, bond paper, recycled paper, transparencies (up to 10 sheets) Multi-purpose tray - plain paper, bond paper, recycled paper, envelopes, labels, transparencies Optional paper tray (LT-5300) - Plain paper, bond paper, recycled paper
Media Weights	Standard paper tray - 60 - 105 g/m <sup>2</sup> Multi-purpose tray - 60 - 161 g/m <sup>2</sup> Optional paper tray (LT-5300) - 60 - 105 g/m <sup>2</sup>
Media Sizes	Standard paper tray- A4, letter, B5 (ISO/JIS), A5, B6(ISO), A6, Exe Multi-purpose tray - Width 69.9 to 215.9 mm, length 116 to 406.4 mm Optional paper tray (LT-5300) - Width 69.9 to 215.9 mm, length 116 to 406.4 mm

### Supplies\*\*\*\*

Standard Yield Toner	TN-3130 - Approx. 3,500 pages*
High Yield Toner	TN-3170 - Approx. 7,000 pages*
Drum	DR-3100 - Approx.25,000 pages

The frequency of replacement of consumables will vary depending on the complexity of the prints, the percentage of coverage, paper size, page per job, and the type of media. For example glossy coated paper will result in a shortened life of such supplies.

### Dimensions & Weights

Dimensions (W x D x H)	With carton 494(W) x 478(D) x 443(H) mm Without carton 371(W) x 384(D) x 246(H) mm
Weights	With carton 11.4kg, without carton 9.5kg

### Others

Power Consumption	Printing	Average 610w
	Standby	Average 80w
	Sleep	Average 8w
Sound Pressure level	Printing	53 dB
	Standby	27 dB
Sound Power level	Printing	6.7B
	Standby	4.3B
Ecology	Power Saving	This enables the printer to consume less energy when not in use.
	Toner Saving	This reduces the toner usage and helps to reduce the total cost of printer ownership.

**Contents**

Toner Cartridge (approx. 2,000 pages\*)  
Drum Unit (25,000 pages)  
Power Supply Cord  
Driver Software for Windows and Mac  
Quick Set-up Guide  
PC Interface cable **NOT** included

- \* Declared yield values at 5% coverage. (Letter/A4)
- \*\* Calculated with 80g/m<sup>2</sup> paper
- \*\*\* Optional free downloads available from <http://solutions.brother.com>
- \*\*\*\* Supplies are available to buy from:
  
- † Windows® only