



Product data sheet

Power tools for trade & industry

Angle Grinder

GWS 20-230 P



Light weight, strong results: compact 230-mm angle grinder with PROtection switch

The most important data

Rated input power	2,000 W
No-load speed	6,500 rpm
Disc diameter	230 mm

Part Number 0 601 8C1 171

[> More product information](#)

Technical data

Technical data

Rated input power	2,000 W
No-load speed	6,500 rpm
Grinding spindle thread	M14
Disc diameter	230 mm
Rubber backing pad, diameter	230 mm
Wire cup brush, diameter	100 mm
Weight	5.5 kg
Switch	PROtection Switch
Packaging dimensions (width x length x height)	190 x 574 x 118 mm
Voltage, electrical	230 V

Noise/vibration information

Surface grinding (roughing)

Vibration emission value ah	5.5 m/s ²
Uncertainty K	1.5 m/s ²

Sanding with sanding sheet

Vibration emission value ah	2.5 m/s ²
Uncertainty K	1.5 m/s ²

**BOSCH**

Invented for life

Product data sheet

Power tools for trade & industry

Advantages:

- High material removal rate of new 2,000-W motor ensures strong cutting results
- Lower heating of overall motor system and improved contact between the motor and carbon brushes for longer lifetime
- PROtection switch for enhanced user protection

