


THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.



NOMINAL DUCT SIZE (W)	C in (mm)	TC in (mm)	HC in (mm)
.5	.69 (17.5)	.040 (1.0)	.230 (5.8)
.75	.94 (23.8)	.050 (1.3)	.240 (6.1)
1	1.25 (31.8)	.060 (1.5)	.350 (8.9)
1.5	1.75 (44.5)	"	"
2	2.25 (57.2)	"	"
2.5	2.75 (69.9)	"	"
3	3.25 (82.6)	.065 (1.6)	.370 (9.4)
4	4.25 (108.0)	"	"
6	6.25 (158.8)	.080 (2.0)	"

PART NO. SYSTEM COVER EXAMPLE
 TYPE → C → LG → LENGTH (ft)
 WIDTH → COLOR →

- SEE CURRENT CATALOG FOR ADDITIONAL PART NUMBER SUFFIXES TO INDICATE COLOR AND OR PACKAGE QUANTITY.
- DIMENSIONS IN PARENTHESIS ARE METRIC.

CAD FILENAME/LAYERS D34518BA_PVC_COVER_02A

PANDUIT

TINLEY PARK, ILLINOIS

WIRING DUCT COVER FOR "S", "D", "E", "F", "G" DUCT TYPES
 CUSTOMER DRAWING

UNLESS OTHERWISE SPECIFIED, DIMENSIONAL TOLERANCES ARE:
 (.XX) : ANGLES :
 (.XXX) :

UNLESS OTHERWISE SPECIFIED, ALL DIMENSIONS ARE GIVEN IN INCHES, THIRD ANGLE PROJECTION.

REV	DATE	BY	CHK	DESCRIPTION	ECN	R	CUST	SUP
2	8-24-01	JCST	JKG	D. CHANGED TOLERANCE C. MADE "C" A REFERENCE DIMENSION	34518-17	JKG	JKG	
1	2/11/00	JHNU	HIW	B. .18 WAS .125/ 4.5 WAS 3.2 A. REV'D TITLE; ADDED FS AND G DUCT TYPE	34518-17	HIW	HIW	
R	10-29-93	DW	CEF	RELEASED TO PRODUCTION.	34518-17	CEF	CEF	

DRAWN BY	DW	MAT'L
		POLYVINYL CHLORIDE

DATE	CHK'D
10-29-93	CEF

SCALE	DRAWING NO.
NONE	34518-17

DWG	SIZE
34518-17	A