

Han 10A-Cover-Plastic 2Pins, f Easy-Lock



Image is for illustration purposes only. Please refer to product description.

Part number	09 20 010 5402
Specification	Han 10A-Cover-Plastic 2Pins, f Easy-Lock
HARTING eCatalogue	https://b2b.harting.com/09200105402

Identification

Category	Hoods/Housings
Series of hoods/housings	Han A [®]
Type of hood/housing	Protection cover
Description of hood/housing	for bulkhead mounted housings
	for surface mounted housings
	for cable to cable housing
	Thermoplastic
Type	Low construction
	High construction

Version

Size	10 A
Locking type	Single locking lever
Field of application	Standard Hoods/housings for industrial applications

Technical characteristics

Limiting temperature	-40 ... +125 °C
Degree of protection acc. to IEC 60529	IP65
Type rating acc. to UL 50 / UL 50E	4
	4X
	12

Material properties

Material (seal)	NBR
RoHS	compliant



Pushing Performance

Material properties

ELV status	compliant
China RoHS	e
REACH Annex XVII substances	No
REACH ANNEX XIV substances	No
REACH SVHC substances	No
California Proposition 65 substances	Yes
California Proposition 65 substances	Naphthalene

Specifications and approvals

Approvals	DNV GL
-----------	--------

Commercial data

Packaging size	1
Net weight	15 g
Country of origin	Germany
European customs tariff number	85389099
eCl@ss	27440208 Cap for industrial connectors

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[HARTING:](#)

[09200105402](#)