

64193ULT

ULTRA LIFE | Halogen headlight lamps for cars



Areas of application

- Headlight
- Ideal for use in clear-glass headlights

Product benefits

- An ideal daytime running lamp due to long life span
- Up to triple the lifetime (compared to standard halogen lamps)
- 3 year guarantee (on halogen headlight lamps)

Product features

- Modern design with a silver cap (H4/H7)

Product datasheet

Technical data

Electrical data


Power input	75 / 68 W ¹⁾
Nominal wattage	60 W
Nominal voltage	12 V
Test voltage	13.2 V

¹⁾ Maximum

Light technical data

Color temperature	3200 K
Luminous flux tolerance	±15 / ±15 %

Dimensions & weight



Product line drawing

Length	82.0 mm
Diameter	17.0 mm
Product weight	25.90 g

Lifespan

Lifespan B3	300 / 2000 h ¹⁾
Lifespan Tc	700 / 3000 h ¹⁾

¹⁾ Filament 1 / Filament 2

Additional product data

Base (standard designation)	P43t
-----------------------------	------

Product datasheet

Certificates & standards

ECE category	H4
--------------	----

Country specific categorizations

Order reference	64193ULT
-----------------	----------

References / Links

Guarantee terms are available at

▶ www.osram.com/am-guarantee

Disclaimer

Subject to change without notice. Errors and omission excepted. Always make sure to use the most recent release.