

Part #	Package	P _D (W)	I _C (A)	V _{CEO} (V)	V _{CBO} (V)	h _{FE}
BUV10	TO-3	150	25	125	160	20-60
BUV11	TO-3	150	20	220	250	20-60
BUV12	TO-3	150	20	250	300	20-
BUV18	TO-3	250	50	60	120	
BUV19	TO-3	250	50	80	160	
BUV20	TO-3	250	50	125	160	20-60
BUV21	TO-3	250	40	200	250	20-60
BUV22	TO-3	250	40	250	300	20-60
BUV23	TO-3	250	30	325	400	15-60
BUV24	TO-3	250	20	400	450	15-60
BUV25	TO-3	250	15	500	500	15-60
BUV26	TO-220	85	20	90	180	
BUV26A	TO-220	85	20	100	200	
BUV26AF	TO-220Fa	18	20	100	200	
BUV26F	TO-220Fa	18	20	90	180	
BUV27	TO-220	85	15	120	240	
BUV27A	TO-220	85	15	150	300	
BUV27AF	TO-220Fa	18	15	150	300	
BUV27F	TO-220Fa	18	15	120	240	
BUV28	TO-220	85	12	200	400	
BUV28A	TO-220	85	12	225	450	
BUV28AF	TO-220Fa	18	12	225	450	
BUV28F	TO-220Fa	18	12	200	400	
BUV37	TO-3PB	125	15	400	450	20-
BUV39	TO-3	120	25	90	160	
BUV40	TO-3	120	20	125	250	
BUV41	TO-3	120	15	200	300	
BUV42	TO-3	120	12	250	350	
BUV42A	TO-3	120	12	300	400	
BUV46	TO-220	85	6	400	850	
BUV46A	TO-220	85	6	450	1000	
BUV46AFI	TO-220F	30	6	450	1000	
BUV46FI	TO-220F	30	6	400	850	
BUV47	TO-3PB	120	9	400	850	
BUV47A	TO-3PN	120	9	450	1000	
BUV47AFI	TO-3PF	55	9	450	1000	
BUV47AI	TO-3PF	55	9	450	1000	
BUV47B	TO-3PB	120	9	400	850	
BUV47FI	TO-3PF	55	9	400	850	

BUV48	TO-3PN	150	15	400	850	8-
BUV48A	TO-3PN	150	15	450	1000	8-
BUV48AFI	TO-3PF	65	15	450	1000	8-
BUV48AI	TO-3PN	150	15	450	1000	
BUV48B	TO-3PN	150	15	600	1200	
BUV48BFI	TO-3PF	65	15	600	1200	
BUV48C	TO-3PN	125	15	700	1200	
BUV48CFI	TO-3PF	55	15	700	1200	
BUV48CI	TO-3PN	125	15	600	1200	
BUV48FI	TO-3PF	65	15	600	1200	
BUV48I	TO-3PN	125	15	450	1000	
BUV48T	TO-3PN	125	15	400	850	
BUV50	TO-3	150	25	125	250	10-
BUV51	TO-3	150	20	200	300	10-
BUV52	TO-3	150	20	250	350	10-
BUV52A	TO-3	150	20	300	400	10-
BUV56	TO-220	70	9	400	850	
BUV66	TO-220	100	15	400	850	
BUV70	TO-3PN	140	10	550	1300	
BUV82	TO-3PN	100	6	400	850	
BUV83	TO-3PN	100	6	450	1000	
BUV89	TO-3PN	125	8	800	1200	
BUV90	TO-3PN	125	12	400	650	
BUV90F	TO-3PFa	34	12	400	650	