

Part #	Package	P _D (W)	I _C (A)	V _{CEO} (V)	V _{CBO} (V)	h _{FE}
BUL118D	TO-220	60	3	400	700	10-50
BUL1203E	TO-220	100	5	550	1200	14-32
BUL128	TO-220	70	4	400	700	14-40
BUL128D	TO-220	70	4	400	700	8-40
BUL216	TO-220	90	4	800	1600	12-40
BUL310	TO-220	75	5	500	1000	10*
BUL310FP	TO-220F	36	5	500	1000	10*
BUL310XI	TO-220Fa	75	5	500	1600	
BUL312	TO-220	36	5	500	1150	8-
BUL381	TO-220	70	5	400	800	8-
BUL381D	TO-220	70	5	400	800	8-
BUL382D	TO-220	70	5	400	800	8-
BUL38D	TO-220	80	5	450	800	13-32
BUL39D	TO-220	70	4	450	850	4-
BUL416	TO-220	110	6	800	1600	12-40
BUL45	TO-220	75	5	400	700	14-34
BUL49	TO-220	80	5	450	850	4-10
BUL49D	TO-220	80	5	450	850	4-10
BUL510	TO-220	100	10	450	1000	15-45
BUL52B	TO-220	100	8	400	800	15-45
BUL56B	TO-220	85	18	100	250	25-60
BUL58B	TO-220	50	12	100	250	25-60
BUL58D	TO-220	85	8	450	800	5
BUL59	TO-220	90	8	450	800	8-40
BUL6825	TO-220	75	4	400	700	8-40
BUL741	TO-220	60	2.5	400	1050	48-100
BUL742	TO-220	70	4	400	900	35-70
BUL742C	TO-220	70	4	400	1050	48-100
BUL810	TO-3PN	125	15	500	1000	10-40