

RS232 to RS485 converter



Model: STM485B

Specification & Features

- Compatibility: EIA/TIA RS232C standard and RS485 standard
- Interface RS232 side: DB9 female connector.
- Interface RS485 side: DB9 male connector with optional (included) terminal board
- Transmission rate: 300 - 115200bps
- Transmission distance: RS485 max. 1200m, RS232 side max. 5m
- Working mode: asynchronous, half-duplex, differential transmission
- Working environment: -20~70°C, relative humidity 5% - 95%