

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [0357607200](#)
Status: **Active**
Overview: [Splices](#)
Description: Wire Splice, 12-16 AWG, Un-Plated

Documents:

[Drawing \(PDF\)](#) [Packaging Specification PK-35760-002-001 \(PDF\)](#)
[Product Specification PS-35760-003-001 \(PDF\)](#) [RoHS Certificate of Compliance \(PDF\)](#)

General

Product Family	Splices
Series	35760
Crimp Quality Equipment	Yes
Mil-Spec	N/A
Overview	Splices
Product Name	N/A
UPC	800753856684

Physical

Barrel Type	Open
Insulation	None
Material - Metal	Brass
Net Weight	0.226/g
Packaging Type	Reel
Temperature Range - Operating	-30°C to +105°C
Wire Insulation Diameter	3.51mm
Wire Size AWG	12, 14, 16


Electrical

Voltage - Maximum	200V AC (RMS)/DC
-------------------	------------------

Material Info

Reference - Drawing Numbers

Packaging Specification	PK-35760-002-001
Product Specification	PS-35760-003-001
Sales Drawing	SD-35760-002, SD-35760-7**0



Series image - Reference only

EU ELV

Not Relevant

EU RoHS

Compliant

REACH SVHC

Not Contained Per -
ED/30/2017 (7 July
2017)

Halogen-Free

Status

Low-Halogen

**Need more information on product
environmental compliance?**

Email productcompliance@molex.com
Please visit the [Contact Us](#) section for any
non-product compliance questions.

China ROHS

ELV

RoHS Phthalates

Green Image

Not Relevant

Not Contained

Search Parts in this Series

[35760 Series](#)

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Molex:](#)

[35760-7200](#)