



RCA Phono Plugs

174-4356-E, 174-4357-E, 174-4358-E, 174-4359-E



RCA Phono Plugs



Dimensions: In.

SPECIFICATIONS	
Type:	RCA non shielded phono with cable protector
Net weight:	3.5g
Color I.D. ring:	red (174-4356)-E, white (174-4357)-E, yellow (174-4358)-E, black (174-4359)-E
Rating:	34 AC/DC 2A
Insulation resistance:	100 mega Ω min. @ 500VDC
Contact resistance:	30 mili Ω Mac.
Dielectric strength:	250VAC for one minute
Handle:	polyethylene
Center terminal:	brass, nickel plated
Insulator:	ABS resin
Shield contact:	steel, nickel-plated
Center contact:	brass, nickel-plated
RoHS Compliant	

Date Last Revised: 12-7-05

Available from Mouser Electronics
1-800-346-6873
www.mouser.com

KC- 300923

174-4356-E, 174-4357-E, 174-4358-E, 174-4359-E

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Kobiconn:](#)

[174-4359-E](#) [174-4357-E](#) [174-4356-E](#) [174-4358-E](#)