

**PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION**

**Part Number:** [1202540137](#)  
**Status:** **Active**  
**Overview:** Contrinex Inductive and Photoelectric  
**Description:** Contrinex Photoelectric Sensor, M18 Housing, Diffuse, PNP, Changeover, Potentiometer Sensitivity Adjustment, 2m 4-wire PVC Cable, 50mm Housing Length

**Documents:**

[Product Specification 1202540137-000 \(PDF\)](#)      [RoHS Certificate of Compliance \(PDF\)](#)

**General**

Product Family	Sensors
Series	<a href="#">120254</a>
Datasheet Order No	987651-9403
Exclude SD Check	Yes
IP Rating	IP67
Operating Principle	Diffuse
Overview	<a href="#">Contrinex Inductive and Photoelectric</a>
Product Category	Sensors
Product Name	Contrinex
Type	Photoelectric
UPC	191130068937

**Physical**

Connection	Cable (PVC 2m, 4-wire)
Length	50mm
Material - Housing	Chrome Plated Brass
Material - Window	Glass
Output	Changeover
Sensor Housing Size	M18
Temperature Range - Operating	-25° to +55°C

**Electrical**

Polarity	PNP
Switching Frequency	≤ 1000 Hz

**Material Info**

Engineering Number	LTK-1180-103
--------------------	--------------

**Reference - Drawing Numbers**

Product Specification	1202540137-000
-----------------------	----------------



*Series image - Reference only*

**EU ELV**

**Not Relevant**

**EU RoHS**

**Compliant with Exemption 6(c)**

**REACH SVHC**

Not Reviewed

**Halogen-Free**

**Status**

**Not Reviewed**

For more information, please visit [Contact US](#)

China ROHS

ELV

RoHS Phthalates

**China RoHS**

50 Image

Not Relevant

Not Contained

**Search Parts in this Series**

[120254 Series](#)

**PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION**

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Molex:](#)

[120254-0137](#)