

**PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION**

**Part Number:** [0936010674](#)  
**Status:** **Active**  
**Overview:** GWconnect Heavy Duty Connectors (HDC)  
**Description:** GWconnect STD - Standard, Single Lever Bulkhead Mount Housing, Polyamide, with 1 Lever, Right Angle, with Gasket, Size 3A «21x21», M20 Thread, Grey White

**Documents:**

[Drawing \(PDF\)](#) [RoHS Certificate of Compliance \(PDF\)](#)

**Agency Certification**

CSA 256883  
 UL E249674

**General**

Product Family Industrial Connectors / Enclosures  
 Series [93601](#)  
 Comments IP67 with screw gasket.  
 Component Size 3A «21x21»  
 Component Type Single Lever Bulkhead Housing  
 IP Rating IP66, IP67  
 Overview [GWconnect Heavy Duty Connectors \(HDC\)](#)  
 Product Category Heavy Duty Connectors  
 Product Name GWconnect  
 Standard ANSI/UL 50, ANSI/UL 50 E, CSA C22.2 No.94-1-2, EN 61984  
 Type STD  
 UPC 887191842011

**Physical**

Flammability UL 94V-0  
 Housing Color Grey White RAL 9002  
 Lock to Mating Part Yes  
 Material - Gasket NBR  
 Material - Housing Polyamide  
 Material - Lever Polyamide  
 Mounting Style Bulkhead  
 Net Weight 17.000/g  
 Number of Levers 1  
 Packaging Type Bag  
 Thread Size M20  
 Thread Type (M) Metric

**Electrical**

Voltage - Maximum 230V / 400V

**Material Info**

Engineering Number 7803.6225.0

**Reference - Drawing Numbers**

Sales Drawing 936010674-000



*Series image - Reference only*

**EU ELV**

**Not Relevant**

**EU RoHS**

**Compliant**

**REACH SVHC**

Not Contained Per -  
 ED/71/2019 (16 July  
 2019)

**Halogen-Free**

**Status**

**Not Reviewed**

For more information, please visit [Contact US](#)

China ROHS

ELV

RoHS Phthalates

ZZCERT\_CE -

Declaration of

Conformity

**China RoHS**

Green Image

Not Relevant

Not Contained

CER\_4000400719\_00\_000.pdf

**Search Parts in this Series**

[93601](#) Series

**Use With**

Size 3A «21x21» S-A, S-D, and S-Q Inserts