




REV.	DESCRIPTION	DRAWN	CHECKED	APPROVED
A	NEW RELEASE	LJH 05/17/05'	~	LJC 05/17/05'
B	统一尺寸规格	LL 11/16/06'	~	LJC 11/16/06'
C	增加尺寸选项	YCH 07/27/10'		



- NOTES:
- MATERIAL&FINISHES
 - INSULATOR:THERMOPLASTIC(UL 94V-0).
 - CONTACT MATERIAL: COPPER ALLOY.
 - SPECIFICATION
 - CURRENT RATING:1.5 Amp.
 - INSULATION RESISTANCE:1000MΩ Min.
 - DIELECTRIC WITHSTANDING:600VAC.
 - CONTACT RESISTANCE:20mΩMax.
 - OPERATING TEMPERATURE:-40°C TO +105°C.




- PRODUCT NUMBER CODE:
DS1025-02 - X X X X X - X
- Dim. A B C type
1: Type 1
5: Type 5
.....
- CONTACTS TYPE
R:RIGHT ANGLE TYPE
- HOUSING COLOR
B:BLACK
- CONTACT PLATING
8:FULL GOLD FLASH
- CONNECTOR TYPE
P:PLUG
- No.OF CONTACTS
1*2-1*X

TABLE A:

TYPE	Dimension			Pin Length
	A	B	C	
1	4.00	2.80	1.00	10.50
2	5.00	2.50	1.00	11.00
3	5.00	4.75	0.75	13.10
4	3.80	3.80	0.75	11.00
5	2.50	2.80	1.30	9.20
6	3.70	3.00	1.75	11.00
7				

N: NUMBER OF CONTACTS
A&B&C: CUSTOMER LENGTH AVAILABLE



RECOMMEND PCB LAYOUT(TOLERANCE=±0.05)

GENERAL TOLERANCE		ANGLE TOLERANCE		PROJECTION	TITLE
X.	±0.60	X.	±5'	mm	SINGLE ROW RIGHT ANGLE
.X	±0.38	.X	±3'		
.XX	±0.25	.XX	±2'		
DRAWING TYPE		CUSTOMER		SHEET SIZE	SERIES
SCALE		1:1		A4	DS1025-02 SERIES
DRAWING NO.		C-DS1025-02-XXXXX-X-C		1 OF 1	

晨翔电子有限公司
CONNFLY CONNFLY ELECTRONIC CO. LTD

TEL: 86-574-63508787
Fax: 86-574-63510817
E-mail: sale@zhenqin.com.cn
Http://www.connfly.com