

sealing ring OL-1/2

Part number: 34637

FESTO

Leak-proof, with metal body.



Data sheet

Feature	Value
Based on the standard	ISO 16030
Container size	1
Operating pressure complete temperature range	-0.95 ... 30 bar
Corrosion resistance classification CRC	2 - Moderate corrosion stress
Ambient temperature	-40 ... 100 °C
Manual tightening at ambient temperature	Yes
Nominal tightening torque	49 Nm
Tolerance for nominal tightening torque	± 20 %
Product weight	2 g
Materials note	Free of copper and PTFE Conforms to RoHS