

**PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION**

**Part Number:** [0192160010](#)  
**Status:** **Active**  
**Description:** Ultimate Wire Tap, Blue, 14-18 AWG

**Documents:**

|                                |  |
|--------------------------------|--|
| <a href="#">3D Model</a>       | <a href="#">Drawing (PDF)</a>                        |
| <a href="#">3D Model (PDF)</a> | <a href="#">RoHS Certificate of Compliance (PDF)</a> |

**Agency Certification**

|     |         |
|-----|---------|
| CSA | LR18689 |
| UL  | E79133  |

**General**

|                         |                           |
|-------------------------|---------------------------|
| Product Family          | IDT and Solder Connectors |
| Series                  | <a href="#">19216</a>     |
| Crimp Quality Equipment | Yes                       |
| Product Name            | Wire Tap                  |
| UPC                     | 800753056282              |

**Physical**

|                                |                 |
|--------------------------------|-----------------|
| Circuits (Loaded)              | 1               |
| Circuits (maximum)             | 1               |
| Color - Resin                  | Natural         |
| Durability (mating cycles max) | 25              |
| Flammability                   | 94V-2           |
| Gender                         | N/A             |
| Glow-Wire Capable              | No              |
| Lock to Mating Part            | None            |
| Material - Metal               | Phosphor Bronze |
| Material - Plating Mating      | Tin             |
| Material - Resin               | Nylon           |
| Net Weight                     | 1.101/g         |
| Number of Rows                 | 0               |
| Packaging Type                 | Bag             |
| Panel Mount                    | No              |
| Pitch - Mating Interface       | N/A             |
| Pitch - Termination Interface  | N/A             |
| Polarized to Mating Part       | Yes             |
| Stackable                      | No              |
| Temperature Range - Operating  | 105°C           |
| Wire Insulation Diameter       | N/A             |
| Wire Size AWG                  | 14, 16, 18      |

**Electrical**


|                   |      |
|-------------------|------|
| Voltage - Maximum | 600V |
|-------------------|------|

**Solder Process Data**

|                              |     |
|------------------------------|-----|
| Lead-free Process Capability | N/A |
|------------------------------|-----|

**Material Info**

|                    |         |
|--------------------|---------|
| Engineering Number | WT-1814 |
|--------------------|---------|



*Series image - Reference only*

**EU ELV**

**Not Relevant**

**EU RoHS**

**Compliant**

**REACH SVHC**

Not Contained Per -  
D(2020)4578-DC (25  
June 2020)

**Halogen-Free**

**Status**

**Low-Halogen**

For more information, please visit [Contact US](#)

China ROHS

ELV

RoHS Phthalates

**China RoHS**

Green Image

Not Relevant

Not Contained

**Search Parts in this Series**

[19216 Series](#)

**Mates With**

Male Quick Disconnect

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Molex:](#)

[19216-0010](#)