


AVERY DENNISON MARKETING SPECIFICATION



NOT TO SCALE

LOOPED TENSILE STRENGTH:	18 LBS. / 80N MINIMUM
OPERATING TEMPERATURE	-4°F (-20°C) TO 185°F (85°C)
MATERIAL:	NYLON 6/6
WEIGHT:	.016 OZ./ .46 GRAMS
BUNDLE DIAMETER:	ø4.76mm/.188" TO ø 22.2mm / .875"
MIN. INSTALLATION TEMP.	5°F (-15°C)
APPLICATION TOOL:	TOOL, HAND ADJUSTABLE, FOR PLASTIC TIE DOWN STRAP. AVERY DENNISON PART NUMBER 12001.
TOOL TENSION SETTING:	1-3
PACKAGED IN:	SEE TABLE



STK.NO	COLOR	PACKAGED IN
08412-2	NATURAL	1000/BAG,5000/CASE
08417-2	NATURAL	100/BAG, 5000/CASE
10031-2	WHITE	1000/BAG,5000/CASE



AVERY DENNISON

FASTENER DIVISION
 FITCHBURG, MA 01420 U.S.A.
 TEL 1-800-225-5913
 MA. 978-353-8157

THESE CABLE TIES HAVE A FLAMMABILITY RATING OF V-2

DESCRIPTION:

4" CABLE TIE, MINIATURE IDENTIFICATION

APPROVAL: Q.A.:

Linda Boyle 625-15

STOCK NO.

SEE TABLE

REV
A

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Avery Dennison:](#)

[08412-0](#) [08412-2](#)