





2150A, 2151A, 2112A, 2152A and 2194A Series Non-Relampable Indicator Lights



Mounting: Ø.310" min., supplied with push-on speednut 8700091652
Lens: Polycarbonate (Neon: Transparent, Incandescent: Translucent)
Bezel: Stainless Steel
Housing: White Nylon
Wire Leads: No. 22 AWG (105°C), 4.40"/4.80" long, stripped .430"/.570"
Current: 1.9mA



Speed Nut 8700091652

Dimensions in inches



| Lens Color | Neon | | Incandescent | |
|------------|------------------------|------------------------|-----------------|-----------------|
| | Model No. (105-125VAC) | Model No. (208-250VAC) | Model No. (12V) | Model No. (28V) |
| Red | 2150A1 | 2151A1 | 2194A1-12V | 2194A1-28V |
| Clear | 2150A2 | - | - | - |
| Amber | 2150A3 | 2151A3 | 2194A3-12V | 2194A3-28V |
| White | 2150A4 | 2151A4 | - | 2194A4-28V |
| Green | 2152A5* | 2153A5* | 2194A5-12V | 2194A5-28V |
| Blue | 2152A6** | 2153A6** | - | - |
| Lamp used | C2A+Resistor | C2A+Resistor | #2162 | #2187 |
| Lead Color | Black | Black/Red | Yellow | Purple |
| "A" DIM | 1.310 | 1.310 | .830 | .830 |

* Incorporates G2B lamp and resistor.

** Incorporates T2B lamp and resistor.

Underwriters Laboratories(UL) File No. E20356

Compliance & Approvals



Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

VCC:

2152A5