


### Deep groove ball bearings, single row, seal on both sides

Principal dimensions			Basic load ratings		Fatigue load limit $P_u$	Speed ratings		Mass	Designation
d	D	B	dynamic	static		Reference speed	Limiting speed		
mm			kN		kN	r/min		kg	-
20	42	12	9,95	5	0,212	-	11000	0,069	6004-2RSH *



**Calculation factors**

$k_r$  0,025  
 $f_0$  14