

Double-poles Rocker Switch

Q-1260

TYPE: **SC-787**

SPECIFICATIONS

Contact Type: DPDT
Rating: 16A 250V AC
Contact R: 35mΩ max
Insulation R: 500V DC 100MΩ min
Dielectric Strength: 1 Minute 1500V AC
Operating Temperature: -25°C ~ +85°C
Electrical Life: 10, 000 Cycles

Outline Drawing

