


solenoid coil

VACF-B-B2-7

Part number: 8030803

FESTO

Type B connection pattern, industry standard, 48 V DC



Data sheet

Feature	Value
Assembly position	Any
Duty cycle	100 %
Insulation class	H
Characteristic coil data	48 V DC: 3.4 W
Permissible voltage fluctuation	+/- 10 %
Maritime classification	see certificate
Certificate issuing department	DNVGL-TAA000011J
Corrosion resistance classification CRC	2 - Moderate corrosion stress
Medium temperature	-20 ... 50 °C
Protection class	IP65
Ambient temperature	-20 ... 50 °C
Electrical connection	To industry standard (11 mm) Plug pattern type B to EN 175301-803
Mounting type	With knurled nut
Materials note	Conforms to RoHS
Material housing	PA Steel
Material solenoid coil	Copper Steel Thermoplastic
Material winding	Copper