


LED Flexible Tape - Digital RGB Tape

A new innovative range of digital RGB Flexible Tape that will bring a colourful feature to any room. suitable for connection to one of our RF digital controllers.



Product Features

- ★ Dynamic colour chasing modes
- ★ Cascading connectors
- ★ High quality UV stable polyurethane coating enables non discolouration and is scratch resistant for longer life
- ★ High grade thick 3M adhesive backing for easy installation
- ★ Available in IP65, IP67 & IP68 ratings
- ★ 50,000 hours working life
- ★ Multiple applications for commercial and residential environments



0118 970 3856


www.powerled.uk.com



LED Flexible Tape - Digital RGB Tape

LED Flexible Tape - RGB

Part Code	F10-RGBD-12-48
Voltage	12VDC
Power Consumption	11.2W per mtr
LED Qty	48 per mtr
Addressing Range	3 LEDs Addressable
Maximum Cascading Length	50M
Colour	RGB
IP	IP22/67/68
IP Finish	Glue filled silicon tube
Back Adhesive	VHB 3M adhesive tape
Working Temperature	-30°C ~ +70°C
Dimensions	5000 x 15.4 x 6.3mm



NEW!

LED Flexible Tape
IP rating part codes
ie: F10-RGBD-12-48-22 ~ IP22
F10-RGBD-12-48-67 ~ IP67
F10-RGBD-12-48-68 ~ IP68




Functions

Dynamic Mode	99 modes
Dynamic Speed Levels	10 levels
Static Colour	29 Colours
Static Colour Brightness	10 Levels

LED Dimmer Unit

Power Connection	5.5mm DC female jack
Strip Connection	4-Pin SM type connector on both ends

Digital RGB LED Flexible Tape



NEW!



Professional RF Wireless RGBW LED Controller Kit

RGBW Digital LED tape can be controlled by the Professional RF Wireless RGBW LED Controller.

LED Flexible Tape - RGB-W Tape

NEW!

LED Flexible Tape - RGB-W

Part Code	F10-RGBW-12-60
Voltage	12VDC
Power Consumption	9.6W per mtr
LED Qty	30 per mtr (30 x RGB & 30 x white)
Cut Points	100mm
PCB Width	15mm (end) 13mm (narrowest point)
White & RGB Colour mixing	Parallel in line
IP	IP20/65/67
IP Finish	Glue filled silicon tube
FPC Material	35um rolled copper fpc
Back Adhesive	VHB 3M adhesive tape
Working Temperature	-30°C ~ +70°C
Strip Connector	5-Pin SM type connector on both ends ~ Simple trouble free connection
Dimensions	5000 x 15 x 6.3mm



LED Flexible Tape IP rating part codes

ie: F10-RGB-W-12-60-22 ~ IP22
F10-RGB-W-12-60-67 ~ IP67
F10-RGB-W-12-60-68 ~ IP68

