

## Product

### AKL 3-t



#### Entries

Entries end:

15 x M20

2 x M20/M25

1 x M32/M40

Entries on each side:

12 x M20

3 x M25/M32

Empty Enclosure, with attachment bushes, sealing and insulating plugs, base: polystyrene, grey, similar to RAL 7035, cover: polycarbonate, transparent

**Article:** AKL 3-t

#### Technical Data

##### Dimensions:

Height: 132 mm

##### material:

Base: Polystyrene, grey, similar to RAL 7035

Cover: Polycarbonate, transparent

Sealing: Polyurethane

Cover screw: Polyamide 6, fiber-glass reinforced

##### Properties:

Ingress protection: IP65 - acc. EN 60529 / DIN VDE 0470-1

Ambient temperature (min.): -25 °C

Ambient temperature (max.): 40 °C

Ambient temperature (24 h): 35 °C

Max. rel. humidity at 25° C (short

Therm): {50%}

Rated insulation voltage AC: 690 V

Impact resistance:	IK07 acc. DIN EN 5012 / VDE 0470 Part 100
Halogen-free:	√
PVC-free:	√
Heavy metals-free:	√
Silicone-free:	√
UV resistance:	-
Combustion behaviour to UL:	HB acc. UL94
Combustion behaviour to VDE:	650°C acc. VDE 0471/ EN 60695
Knockouts:	√

---

---

**Manufacturer**

Günther Spelsberg GmbH + Co. KG  
Im Gewerbepark 1  
58579 Schalksmühle  
+49 (0)2355/892-0  
+49 (0)2355/892-299  
[www.spelsberg.de](http://www.spelsberg.de)