

Cable - CABLE-D25SUB/S/S/300/KONFEK/S - 2305651

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://download.phoenixcontact.com>)

Assembled, shielded circular cable, with D-SUB pin strip, 25-pos. from both sides, cable length: 3 m



Key commercial data

| | |
|--------------------------------------|---|
| Packing unit | 1 pc |
| GTIN |  4 046356 011990 |
| Weight per Piece (excluding packing) | 516.5 g |
| Custom tariff number | 85444290 |
| Country of origin | Germany |

Technical data

General

| | |
|---|--|
| Nominal voltage U_N | 125 V AC/DC |
| Max. current carrying capacity per path | 2 A |
| Max. conductor resistance | $\leq 0.09 \Omega/m$ |
| Length of cable | 3 m |
| Single wire, cross section | 0.25 mm ² |
| AWG | 24 |
| External diameter | 10.5 mm |
| Shielding | yes |
| | Tinned copper-braided shield, approx. 85% covering |
| Insertion/withdrawal cycles | > 200 |

Environmental conditions

| | |
|---|------------------|
| Ambient temperature (operation) | -20 °C ... 50 °C |
| Ambient temperature (storage/transport) | -20 °C ... 70 °C |
| Flame resistance | IEC 60332-1 |

Connector, module side

| | |
|---------------------|-----------------|
| Number of positions | 25 |
| Connectors | D-SUB pin strip |
| Number of plugs | 1 |

Cable - CABLE-D25SUB/S/S/300/KONFEK/S - 2305651

Technical data

Connector, controller side

| | |
|---------------------|-----------------|
| Number of positions | 25 |
| Connectors | D-SUB pin strip |
| Number of plugs | 1 |

Classifications

eCl@ss

| | |
|------------|----------|
| eCl@ss 4.0 | 27060306 |
| eCl@ss 4.1 | 27060306 |
| eCl@ss 5.0 | 27061801 |
| eCl@ss 5.1 | 27061801 |
| eCl@ss 6.0 | 27061801 |
| eCl@ss 7.0 | 27061801 |
| eCl@ss 8.0 | 27061801 |

ETIM

| | |
|----------|----------|
| ETIM 2.0 | EC000237 |
| ETIM 3.0 | EC000237 |
| ETIM 4.0 | EC000237 |
| ETIM 5.0 | EC000830 |

UNSPSC

| | |
|---------------|----------|
| UNSPSC 6.01 | 26121620 |
| UNSPSC 7.0901 | 26121620 |
| UNSPSC 11 | 26121620 |
| UNSPSC 12.01 | 26121620 |
| UNSPSC 13.2 | 26121620 |

Approvals

Approvals

Approvals

UL Recognized / cUL Recognized / cULus Recognized


Ex Approvals


Approvals submitted

Cable - CABLE-D25SUB/S/S/300/KONFEK/S - 2305651

Approvals

Approval details

UL Recognized 

cUL Recognized 

cULus Recognized 