

AK 10 blau/blue

Hirschmann Automation and Control GmbH:Industrial Connectors:Measuring and Testing Equipment:Alligator clips:4 mm system

Product description

Description Insulated alligator clip. Clamping range up to 6 mm bolt diameter. Fine wire section for very thin wires. Only the lower part of the clip has a tin-plated, brass contact insert. 4 mm diameter socket connection.

Type AK 10 blau/blue

Order No. 930 126-102

System 4 mm system


Clamping range 6 mm

Housing Color blue



Other standard types
 black color,
 order no. 930 126-100;
 red color,
 order no. 930 126-601;
 yellow color,
 order no. 930 126-103;
 green color,
 order no. 930 126-104

Drawing



Technical data

Type of contact	socket
Type of termination	4 mm socket
Rated voltage	DC 60 V
Rated current	6 A
Contact resistance	15 mOhm
Material	
Contact material	brass
Contact surface material	tinned
Housing material	PS
Environmental conditions	
Temperature range	-25 °C to +60 °C
Inflammability class	
Housing	94 HB