

## UAR125x32-Ø12 HL44,4 red

EAN 4031582323139

Wheel centre made of Polyamide, Tread: Polyurethane, roller bearing

### Technical Data

Wheel diameter	125 mm
Width of Tread	32 mm
Axle Hole-Ø	12 mm
Hub length	44.4 mm
Temperature	- 40 / + 80 °C
Standard	EN 12532
Weight	0.266 kg
Hardness of tread	Shore D 40
Load capacity	200 kg
Load capacity (static)	400 kg



Roll performance	+	+	+	+	+
Movement noise	+	+	+	+	+
Attrition	+	+	+	+	+
Corrosion resistance	+	+	+	+	+

