

May not be suitable for all medical and aerospace applications.

Specifications: Contact Mallory Sonalert to discuss your application.

Voice Coil Impedance (Ω)	$8 \pm 15\%$ at 600 Hz / 1.0 V
Rated Input (W)	0.5
Max. Input (W)	0.80
Lowest Resonance Freq Fo (Hz)	$450 \pm 20\%$
Frequency Range (Hz)	Fo ~ 10000
Output S.P.L. (dB)	83 ± 3 at 0.5W 0.1M 1k, 1.2k, 1.5k, 2.0Khz 86 ± 3 at 1W 0.1M 1k, 1.2k, 1.5k, 2.0Khz
Magnet	Ferrite
Core Material Mylar	Transparent Radial
Frame Material	Plastic
Operation / Storage Temp	-25 to 50°C / -25 to +55°C
Options	For other options contact factory

Dimensions: (units: mm)

ROHS Compliant

