

STAF 14 STI-S



Image is for illustration purposes only. Please refer to product description.

Part number	09 70 014 2614
Specification	STAF 14 STI-S
HARTING eCatalogue	https://b2b.harting.com/09700142614

Identification

Category	Inserts
Series	Staf®

Version

Termination method	Screw termination
Gender	Male
Size	10 A
Number of contacts	14

Technical characteristics

Conductor cross-section	1.5 mm ²
Rated current	10 A
Rated voltage	25 V
Rated voltage	25 V AC 60 V DC
Rated impulse voltage	0.8 kV
Pollution degree	3
Rated voltage acc. to UL	50 V
Rated voltage acc. to CSA	50 V
Insulation resistance	>10 ¹⁰ Ω
Contact resistance	≤2 mΩ
Tightening torque	0.25 Nm
Limiting temperature	-40 ... +100 °C



Pushing Performance

Technical characteristics

Mating cycles	≥500
---------------	------

Material properties

Material (insert)	Polyamide (PA)
Colour (insert)	Black
Material (contacts)	Copper alloy
Surface (contacts)	Silver plated
Material flammability class acc. to UL 94	HB
RoHS	compliant with exemption
RoHS exemptions	6(c): Copper alloy containing up to 4 % lead by weight
ELV status	compliant with exemption
China RoHS	50
REACH Annex XVII substances	No
REACH ANNEX XIV substances	No
REACH SVHC substances	Yes
REACH SVHC substances	Lead

Specifications and approvals

Specifications	EN 60664-1 IEC 61984
UL / CSA	UL 1977 ECBT2.E235076

Commercial data

Packaging size	1
Net weight	40.4 g
Country of origin	Romania
European customs tariff number	85366990
eCl@ss	27440205 Contact insert for industrial connectors

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[HARTING:](#)

[09700142614](#)